



Region
Global > North America > Europe

English | 中文 (简体) | 日本語

Home

Products

Search

Support

About Us

[Home](#) > [Search Engine](#) > Catalog: CDBC455KCAY66-R0

Filters for Communication Equipment > for IF > Ceramic Discriminators (455kHz)

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	Obsolete
Replacement	CDBKB455KCAY66-R0

Specifications

Global Part Number	CDBC455KCAY66-R0
Previous Part Number	CDBC455CX66
Nominal Center Frequency (fn)	455kHz
Recovered Audio 3dB BW	fn±4.2kHz min.
Recovered Audio Output	40mV ±10
Distortion (at fn)	4.0% max.
Distortion	
Area of Distortion	
S Curve (1) Output Volt. at fn	
S Curve (2) at fn±4.8kHz	
Inclination of Impedance Curve (1)	
Inclination of Impedance Curve (2)	
Anti-resonant Frequency (Fa)	
Delta F (Fa-Fr)	
Resonant Resistance (R)	
Capacitance (C)	
IC	NJM2590
IC Maker	JRC
Last Time Buy	JUNE 2006

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features_and_Applications](#)
-  [Frequency_Characteristics](#)
-  [Test_Circuit](#)
-  [Standard_Land_Pattern_Dimensions](#)
-  [Notice](#)
-  [Packaging](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	500
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Product specifications in this catalog are as of July 2013
Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.

UP ^

