

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638191300

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 18-24 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Taxonomy

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

See Tooling Specification (PDF) Above; Type: 4D Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Crimp Presses and Crimp Hand T

Hand Crimp Tool

80075695582

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

332.600/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638191300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

Standard .062" Pin and Socket Crimp Terminals, 18-24 AWG

Application Tooling Description	FAQ Product #
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	2061101
1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	2062101

	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag	2062103
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	2065100
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	2065101
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag	2065102
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag	2065103
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	2065108
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag	2065109
	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Reel	2066100

	1.57mm Diameter, 2066101 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Reel Packaged
	1.57mm Diameter, 2066102 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with .76µm Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Bag Packaged
	1.57mm Diameter, 2066103 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 18-24 AWG, Bag
	1.57mm Diameter, 2066118 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Reel
	1.57mm Diameter, 2066119 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Selective Gold (Au) Plated Brass Contact, Tin/Lead Plated Crimp Area, 18-24 AWG, Bag
	1.57mm Diameter, 39000278 Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel