

Representative Image

Catalog No. GSC425

Description: 2-PC OUTER SLVE CONN SLV I.D. 0.425

UPC No 786210814049

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .425 Inches/10.80mm, Outer Diameter .475 Inches/12.06mm, Color Silver, Soft Bronze, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Outer sleeve for the Hexagonal Range (the outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

Specifications

Material	Soft Bronze
Color	Gray

Classifications

Brand Name	Sta-Kon
Sub Brand	Shield-Kon

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002650 Connection for screened wires
Model	2-part
Sleeve form	Outer sleeve
Insulated	N
Outer diameter sleeve	12.06 mm
Inner diameter sleeve	10.8 mm
Sleeve length	6.4 mm
Sleeve length	0.25 inch

by ABB

Downloaded from Arrow.com.

ETIM	EC002650 Connection for screened wires
Colour code	Silver
Compression shape	Round
Reel packaging	N

Downloaded from Arrow.com.