


Type: 010606038

External dimensions: 64 x 58 x 34 mm


Weight: 165 g

	DIN rail length in mm
	max. fitting length in mm
	Earthing rail clamp
	Mounting plate (thickness in mm)
	External mounting brackets
	External hinge* set
•	EMC version
	Internal hinge* set
•	SWB / SBG / SBGL Corr. protection
•	Allen lid screws
•	Silicone lid seal
•	Sealable lid screws In steel
	Turn bolt fastener on request
	Quick lock


Maximum number of
cable glands to DIN 50262*



M	Corner dim.	Side		PG	Corner dim.	Side	
		A B	C D			A B	C D
12	17.25	2	1	7	17.25	2	1
16	25.30			9	21.85	1	1
20	27.60			11	25.30		
25	37.95			13.5	27.60		
32	48.30			16	31.05		
40	60.95			21	37.95		
50	69.00			29	48.30		
63	74.75			36	60.95		
				42	69.00		
				48	74.75		



* - Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



DATE	17 MAY 2017	7330 Executive Way Frederick, MD 21704 (301) 696-9411 voice (301) 696-9494 fax	
SHEET	1		
DESCRIPTION		ENCLOSURE, STANDARD, ALUMINUM 64 X 58 X 34MM, UNPAINTED	
SIZE	DRAWING NUMBER		REV
A	010606038		-