Part Number : 1301380082
Product Description : Watertite Multiple Outlet Pendant Box, GFCI, (1)NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Series Number : 130138
Status : Active
Product Category : Power Distribution
Engineering Part Number : 70W33M123GF



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Relevant

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130138
Description	Watertite Multiple Outlet Pendant Box, GFCI, (1)NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Watertite
Type	Multiple Outlet Box
UPC	78678828312

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	120V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	4.57m (15.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable

Downloaded from Arrow.com.

Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on May 09, 2026

Downloaded from Arrow.com.