

SKINDICHT® BLK-M

SKINDICHT® BLK-M, blind plugs for closing pre-threaded holes, cost-effective solution made from Polystyrol



Reliability



UV-resistant



Waterproof

Benefits

For closing pre-threaded holes
Cost-effective solution

Application range

Control cabinet manufacturing
Distribution box
Junction boxes

Product features

Assembling with screwdriver

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Last Update (30.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® BLK-M

Colour delivered:	Light grey (RAL 7035)
Material:	Impact-resistant polystyrene
Protection rating:	IP 54 IP 68 (with O-Ring)
Temperature range:	-25°C to +60°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® BLK-M

Article number	Article designation / size	Thread length D mm	Pieces / PU
SKINDICHT® BLK-M			
52006600	M 12 x 1,5	6	100
52006610	M 16 x 1,5	6	100
52006620	M 20 x 1,5	6	100
52006630	M 25 x 1,5	8	100
52006640	M 32 x 1,5	8	50
52006650	M 40 x 1,5	8	25
52006660	M 50 x 1,5	10	25
52006670	M 63 x 1,5	12	25

Last Update (30.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16