

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1062250011

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 4.80mm, Singlemode, 12 Fiber, Plenum, OS2, 50.0m Length, Yellow



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Fiber Optic Assemblies
Series	106225
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Overview	Optical Connectivity Solutions
Product Name	MPO
UPC	191128250238
Physical	
Cable Length	50.0m
Cable Size	4.80mm
Fiber (Core/Cladding)	9/125µm
Net Weight	1092.453/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum
Material Info	
Reference - Drawing Numbers	
Sales Drawing	1062250000-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

106225 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION