

5

4

3

2

1



Description: CAT5E molded & booted patch cable
 Part No: 73-779X-XXX
 Application: Patch cable
 Crimp Tool: N/A
 Impedance: N/A
 Frequency Range: N/A
 Material: Plug RJ-45, Gold plated on contacts
 Hood PVC
 Cable UTP, 24 AWG, 4 twisted pairs, stranded bare copper, UL ETL EIA/TIA-568B verified category 5e

DRAWING NO.
73-779X-XXX-CUST


REVISIONS

OFFICIAL RELEASE					
01	03-28-11	J	J	D	


RoHS Compliance: Yes
 Technical Detail: N/A

TABLE 1

PART NUMBER	LENGTH (FEET)	DESCRIPTION
73-779X-1	1	CAT5E MOLDED & BOOTED PATCH CABLE, 1FT
73-779X-1.5	1.5	CAT5E MOLDED & BOOTED PATCH CABLE, 1.5FT
73-779X-3	3	CAT5E MOLDED & BOOTED PATCH CABLE, 3FT
73-779X-5	5	CAT5E MOLDED & BOOTED PATCH CABLE, 5FT
73-779X-7	7	CAT5E MOLDED & BOOTED PATCH CABLE, 7FT
73-779X-10	10	CAT5E MOLDED & BOOTED PATCH CABLE, 10FT
73-779X-14	14	CAT5E MOLDED & BOOTED PATCH CABLE, 14FT
73-779X-25	25	CAT5E MOLDED & BOOTED PATCH CABLE, 25FT
73-779X-50	50	CAT5E MOLDED & BOOTED PATCH CABLE, 50FT
73-779X-100	100	CAT5E MOLDED & BOOTED PATCH CABLE, 100FT



X=COLOR
 0-GRAY
 1-BLACK
 2-BLUE
 3-GREEN
 4-RED
 5-YELLOW
 6-WHITE
 7-ORANGE
 8-PINK
 9-PURPLE



CUSTOMER COPY

DIM OUTLINE

受控 CONTROLLED DOCUMENT					
编号 P/N	73-779X-XXX-CUST	版本 Rev	01	日期 Rel'd Date	Jul11,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	JEAN.JIN	03-28-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	JEAN.JIN	03-28-11
X.XX	±0.15	APPROVED BY	DATE
ANGLES	± 0.5°	DONALD	03-28-11
		U/M	mm

TITLE		
CAT5E MOLDED & BOOTED PATCH CABLE		
SHEET	DRAWING NO.	SIZE
1 OF 1	73-779X-XXX-CUST	A

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1