




REV.	DATE	DESCRIPTION
A	06/29/04	UPDATE DRAWING FORMAT
B	03/27/05	ADD 17.5 HEX DIMENSION



- CRIMP NOTES:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
 2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE .7mm
 3. MAX. PANEL THICKNESS= 5.5mm

Amphenol Connex TNC BULKHEAD CRIMP JACK (FOR RG-178B/U, 196A/U CABLE) 122370										
PART NO.		122370								
SHEET 1 OF 1										
ISSUED										
CHECKED										
DRAWN		G.R.S.		03/27/05		DATE			APPROVALS	
DO NOT SCALE DRAWING		QTY		FINISH		MATERIAL		DESCRIPTION		
1		1		NICKEL		BRASS		BODY		
2		1		NATURAL		DELIRIN		INSULATOR		
3		1		GOLD		BRASS		CONTACT PIN		
4		1		RED		RUBBER		GASKET		
5		1		NICKEL		BRASS		LOCK WASHER		
6		1		NICKEL		BRASS		HEX NUT		
7		1		NICKEL		COPPER		FERRULE		
8										