

Han A Hood Coupler Thermoplastic 1 Lever



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0727
Specification	Han A Hood Coupler Thermoplastic 1 Lever
HARTING eCatalogue	https://b2b.harting.com/19200030727

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Cable to cable housing

Version

Size	3 A
Version	Top entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate (PC)
-------------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	10
Net weight	12 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140124493
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors