



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL



UTP28SP15VL

Category 6 Performance, 28 AWG UTP patch cord with TX6™ Modular Plugs on each end.

Specs

Documents

★ Add to Favorites

Add to BOM

Std. Pkg. Qty. 1

Product Type Copper Patch Cord

Performance Level Category 6/Class E

Cable Type U/UTP

Cable Color Violet

Length (ft.) 15.00

Length (m) 4.6

Flammability Rating Dual Rated (CM/LSZH)

Termination End 1 Modular Plug

Termination End 2 Modular Plug

Standards PoE,PoE+

Wiring Scheme T568B

CE Compliant Yes

Nominal Cable O.D. (In.) 0.15

Nominal Cable O.D. (mm) 3.8

Operating Temperature 14°F to 140°F (-10°C to 60°C)

Storage Temperature -40°F to 158°F (-40°C to 70°C)

UL5A Listed -

Conductor Material Copper

RoHS Compliance Status Compliant

Min. Order Qty. 1.0000