

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:**

**0638114200**

**Status:**

**Active**

**Overview:**

Application Tooling

**Description:**

PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 18-22 AWG

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family

Application Tooling

Series

207129

Comments

Prototype and field repair. Type: 4A

Function

Crimp

Geographic Area

Global

Level of Automation

Manual

More Detailed Tech Information

[applicationtooling@molex.com](#)

Overview

[Application Tooling](#)

Product Name

N/A

Tool Type

Hand Crimp Tool

UPC

756054736920

Warranty Disclaimer

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight

428.885/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents

ATS-6381142HM-001, TM-638000029-001,  
TM-638000029CN-001, TM-638000029DE-001,  
TM-638000029FR-001, TM-638000029IT-001,  
TM-638000029JP-001, TM-638000029KR-001,  
TM-638000029MY-001, TM-638000029PL-001,  
TM-638000029RU-001, TM-638000029SK-001,  
TM-638000029SP-001, TM-638000029TH-001,  
TM-638000029TW-001, TM-638000029VN-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

207129 Series

**Use With**

Loose Piece Terminals

**Application Tooling | FAQ**

**Description**

**Product #**

2.54mm Pitch MX64 [334670003](#)

Terminal, Gold

(Au) Plating, 22

AWG, Right Reel

Payoff, Also used

with MX123 Female

Receptacle Housing

2.54mm Pitch MX64 [334670004](#)

Terminal, Gold

(Au) Plating, 22

AWG, Left Reel

Payoff, Also used

with MX123 Female

Receptacle Housing

2.54mm Pitch MX64 [334670005](#)

Terminal, Gold

(Au) Plating, 18-20

AWG, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [334670006](#)  
Terminal, Gold  
(Au) Plating, 18-20  
AWG, Left Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [334680001](#)  
Terminal, Tin (Sn)  
Plating, 22 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [334680002](#)  
Terminal, Tin (Sn)  
Plating, 22 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [334680003](#)  
Terminal, Tin (Sn)  
Plating, 18-20 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [334680004](#)  
Terminal, Tin (Sn)  
Plating, 18-20 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [347361001](#)  
Terminal, Silver  
Plating, 22 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [347361002](#)  
Terminal, Silver  
Plating, 18-20 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [347362001](#)  
Terminal, Silver  
Plating, 22 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 [347362002](#)  
Terminal, Silver  
Plating, 18-20 AWG,  
Right Reel Payoff,  
Also used with

This document was generated on 06/25/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**