
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE		DIMENSIONS - in. [mm]					TOOLS
	ENGLISH	METRIC	L± .04 [1,1]	W± .01 [0,3]	C± .01 [0,3]	M± .02 [0,6]	H +.02 [0,4] -0	
EV8-8R	#8	M4	1.18 (30.0)	.31 (8.0)	.37 (9.3)	.66 (16.7)	.17 (4.3)	KST-HDC38A
EV8-14R	1/4"	M6	1.26 (32.0)	.47 (12.0)	.37 (9.3)	.66 (16.7)	.25 (6.4)	
EV8-56R	5/16"	M8	1.5 (38.0)	.59 (15.0)	.54 (13.8)	.66 (16.7)	.33 (8.4)	
EV8-38R	3/8"	M10	1.5 (38.0)	.59 (15.0)	.54 (13.8)	.66 (16.7)	.41 (10.5)	
EV8-12R	1/2"	M12	1.64 (41.7)	.79 (20.0)	.59 (15.0)	.66 (16.7)	.51 (13.0)	



NOTES:

1. UL LISTED FOR:
   A. #8 AWG [8mm²] STRANDED COPPER WIRE
   B. 221°F (105°C) MAX TEMP RATING
   C. 600V MAX VOLTAGE RATING

2. MATERIAL:
   A. STAMPING - .047" (1.2) THICK COPPER, TIN PLATED
   B. HOUSING - VINYL, RED

3. WIRE STRIP LENGTH: 15/32" $^{+1/32}_{-0}$ (12mm $^{+.8}_{-0}$)

4. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES

5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

c UL us
LISTED
20U0
E52164

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	9/22	JHNU	JHNU	JADE	REVISED DIMENSION C TO REFERENCE CENTER OF STUD HOLE	125881
00	2/18	JHNU	TMR	RGB	DRAWING RELEASED	00123SS

TITLE
STRONGHOLD RING TERMINAL
VINYL INSULATED, BRAZED SEAM #8 AWG [8mm²]
CUSTOMER DRAWING

ITEM REVISION NAME: 00123SSB/01
DATASET FILE NAME: 00123SSB/01

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ±
.XX ± ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: SEE NOTES

DRAWING NUMBER: 00123SSB-DC

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JHNU	2/18	TMR	NONE		A

D10100DA/16

Downloaded from Arrow.com.