




Material Datasheet

13.02.2023

HA67-19.0/3.2
Article Number 321-30000



Material:	Polyolefin, cross-linked (PO-X)
Colour:	Black (BK)
Adhesive:	Hot melt adhesive
Supplied Ø D min.:	19.0 mm
Recov. Ø d max.:	3.2 mm
Wall (WT):	3.2 mm
Shrink Ratio:	6:1
Longitudinal Change After Shrinkage:	-10% max.
Min. Shrink Temperature - °C:	+120 °C

Test Method

Flammability:	not flame-retardant
Operating Temperature :	-55 °C to +110 °C, (outer wall only)

Dielectric Strength:	20 kV/mm	IEC 243
Tensile Strength:	14 MPa	
Elongation at break:	≥400%	
UV-Stabilised (Yes/No):	No	



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved