

1-1634010-0 Product Details

 Share  Print  Email



 Active

MMCX RF Connectors

MMCX R/A PCB Skt 50ohm Gold Pl

1-1634010-0 

TE Internal Number: 1-1634010-0

Product Highlights [View All](#)

- Connector Style = Jack
- Applies To Printed Circuit Board
- Body Style = Elbow
- Not Surface Mountable
- RoHS compliant, ELV compliant

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback


Documents


Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
Grade	Professional 
Mounting Post Style	Straight
Mounting Hole Diameter (mm [in])	5 x .800 [.197 x .031]
Dielectric Material	PTFE
PCB Mount Retention Type	Solder Tail (Pin)
Mechanical Attachment	
Surface Mountable	No
Electrical Characteristics	
Connector Impedance (Ω)	50
Dimensions	
Mounting Post Length (mm [in])	3.00 [0.118]
PCB Height (mm [in])	3.80 [0.150]
Body Features	
Body Style	Elbow
Body Material	Brass
Body Plating	Gold
Body Shape	Square
Contact Features	
Center Contact Material	Beryllium Copper
Center Contact Plating	Gold

Housing Features	
Connector Style	Jack 
Configuration Features	
Bulkhead Jack	No
Industry Standards	
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
Environmental	
Operating Temperature (Max.) (°C)	165
Conditions for Usage	
Applies To	Printed Circuit Board
Packaging Features	
Packaging Method	Individual
Packaging Quantity	50
Other	
Brand	Greenpar

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)