

T 3435 502 U



Data Overview

Description:	Female Plug; 7 Pin; Solder; Silver; 6-8mm; IP40
rated voltage	300 V
number of positions (w/o PE)	7
rated current (40 °C)	7 A
termination	solder pin
contact plating	silver
IP-class mated	IP40

Product Availability	Currently not on stock
Packing Unit:	105 Pieces
Min. Order Quantity:	105 Pieces

Price per Piece:	€4.51
Total Price plus VAT:	€473.55

[Send Request](#) ✉

105 [Add to Cart](#)

[Stock of our Distributors](#) ▾

Technical Data

General Characteristics +	
part category	female cable connector
gender	female
locking system	bayonet ring
housing style	straight
minimum cable diameter	6 MM
maximum cable diameter	8 MM
lower temperature	-40 GC
upper temperature	100 GC
IP-class mated	IP40
Electrical Characteristics +	
Further Characteristics +	
Downloads ↓ +	

Frequently Asked Questions

Which components belong to a complete bill of materials (BOM)?	+
Amphenol as a supplier of complete assemblies and plug & play solutions	+
What options are there for direct transfer to a printed circuit board?	+
How does the transmission of the cable shielding work with M16B connectors?	+
Crimping or soldering - what are pros & cons?	+
Tarnishing of silver-plated contacts - what's the reason?	+
What options are there for color adjustments to the application?	+
M16 receptacles with hex nut instead of ring nut?	+
What are the 5 and 7 pole stereo layouts used for?	+
What does the U at the end of the part number stand for?	+

This might interest you

Accessory »

Housing »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

- [Contact](#)
- [Downloads](#)
- [Imprint](#)
- [General Conditions](#)
- [Career](#)
- [Privacy Policy](#)
- [Privacy Settings](#)



Newsletter

E-Mail

I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following [consent](#).

[Subscribe to Newsletter](#)