

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/2/11	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 6T, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 1,000 Mohms min. @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 230°C for 5 seconds

Positions: 10, 20, 30, 40, 50, 60, 70, 80, 90, 100
 A = .050 [1.27] x No. of Spaces + .349 [8.87]
 B = .050 [1.27] x No. of Spaces + .255 [6.47]
 C = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES
 .X ± .10
 .XX ± .020
 .XXX ± .015
 .XXX ± .015
 .XXX ± .010
 .XXX ± .015
 .XXX ± .010

ADAM TECH
 909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710
 .050" x .100" BOX HEADER
 VERTICAL MOUNT

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	AY	3/2/11	HBHR-A-XX-VG	-
CHECKED	VW	3/2/11		
APPROVED				

A

B

C

D

6

5

4

3

2

1