

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202480005

Status:

Active

Overview:

Brad Passive-Signal and Safety MPIS Boxes

Description:

MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 4 Ports, LED for PNP Sensor, WSOR Cable, 10.0m Length

Replacement Part Number :

http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=12011480121201148012



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Passive Distribution Boxes
Series	120248
IP Rating	IP67
Overview	Brad Passive-Signal and Safety MPIS Boxes
Product Name	MPIS
Replacement Part Number	1201148012
UPC	889056140775
Physical	
Bus I/O	N/A
Cable Connector Orientation	Straight
Cable Length	10.0m
Home Run Cable Length	10.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	A-coded
LED Indicator	PNP Sensors
Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	140.000/g
Orientation	Top-Mount
Poles	4
Poles (wired)	4
Ports	4
Temperature Range - Operating	-25°C to +85°C
Wire/Cable Type	WSOR
Wiring Configuration	Single I/O per Port
Electrical	
Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC
Material Info	
Engineering Number	BTB400P-FBW-10
Reference - Drawing Numbers	
Sales Drawing	1202480001-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120248 Series

This document was generated on 08/19/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION