


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1722562104](#)
Status: **Active**
Overview: [Ultra-Fit Power Connectors](#)
Description: Ultra-Fit TPA Receptacle Housing, 3.50mm Pitch, Single Row, 4 Circuits, Natural, Glow-Wire Capable

Documents:

3D Model	Application Specification AS-172323-0001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 1723230001-TS-000 (PDF)	Product Literature (PDF)
Product Specification PS-172323-0001-001 (PDF)	



Series image - Reference only

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	172256
3D Viewer	Yes
Application	Power, Wire-to-Board
Overview	Ultra-Fit Power Connectors
Product Literature Order No	987651-1008
Product Name	Ultra-Fit
UPC	887191734071

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.420/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-172323-0001
Product Specification	1723230001-TS-000, PS-172323-0001-001
Sales Drawing	SD-172256-0001-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172256](#) Series

Mates With

Ultra-Fit Right Angle Header [172310](#)

Ultra-Fit Vertical Header [172286](#) ,
[172287](#)

Use With

Ultra-Fit Female Crimp Terminal [172253](#)

Ultra-Fit TPA Retainer [172264](#)