



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US



Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL

PPMA1667D



Self-Stick Pipe Marker, ---> (Short arrow), Green, Size D.

Sold in US and Canada only

Specs

Packaging Details

Documents



Add to Favorites



Add to BOM

Material	Dura-Polyester Vinyl
Overall Width (mm)	304.8
Overall Height (mm)	63.5
Note	Sold in US and Canada only
Application	Mark and identify contents in pipes and piping systems, including flow directions and hazard classification for maintenance and safety purposes. Pipe markers are designed in accordance to ASME (ANSI) A13.1 recommendations for sizes, colors, and visibility.
Color	White on Green
Diameter (mm)	152.4
Dimensions (In.)	2.5" x 12"
Environment	5-7 years
Legend	--->(SHORT ARROW)
Maximum Operating Temperature (°C)	80
Maximum Operating Temperature (°F)	176
Maximum Overall Height (mm)	63.5
Minimum Operating Temperature (°C)	-28
Minimum Operating Temperature (°F)	-20
Operating Temperature	-20°F to 176°F
Part Features	6-mil thick poly-composite vinyl with permanent acrylic adhesive backing scored liner for quick peel-off to apply onto pipe., Sub-surface image is protected by a high-gloss UV protective coating and is resistant to abrasions, humidity, chemicals, solvents, and fading from sunlight, Includes detachable arrow to provide proper directional flow marking, Fits pipe diameter 2.5" to 6"
Thickness (mm)	0.1016
UL Listed	No
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
Sub Brand	Stock Pipe Markers