


REV.	DATE	DESCRIPTION
NC	07/15/03	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex										
8						DRAWN	G.R.S.	07/15/03												
7						CHECKED			PART DESCRIPTION SMC P.C. MOUNT JACK – 75ohm											
6						ISSUED														
5						SHEET	1 OF 1		PART NO. 152119-75											
4																				
3	CONTACT PIN	BRASS	GOLD	1			CAD FILE		C:/152/152119-75.DWG		DWG. NO.	152119-75.DWG		REV.	NC	SIZE	A	SCALE	NA	
2	INSULATOR	TEFLON	NATURAL	1																
1	BODY	BRASS	GOLD	1																
DESCRIPTION					MATERIAL					FINISH					QTY					