


Part no. 09 15 000				Ø	Wire gauge		Stripping length	Recommended crimping tools				
silver plated		gold plated			mm ²	AWG		09 99 000 0888	09 99 000 0001	09 99 000 0110	09 99 000 0021	
male contact	female contact	male contact	female contact									
6107	6207	6127	6227	0,90	0,14-0,37	26-22	8	X	X			
6104	6204	6124	6224							X	X	
6103	6203	6123	6223	1,10	0,5	20		X	X	X	X	
6105	6205	6125	6225	1,30	0,75	18		X	X	X	X	
6102	6202	6122	6222	1,45	1	18		X	X	X	X	
6101	6201	6121	6221	1,75	1,5	16		X	X	X	X	
6106	6206	6126	6226	2,25	2,5	14		6	X	X		

Note: position of the inspection hole is on the crimp collar for 2.5mm² female contacts and the crimp collar of the 2.5mm² male contacts has no shoulders



 		All Dimensions in mm Original Size DIN A4		Scale 2:1		Free size tol.		Ref.		
								Sub.		
		All rights reserved		Created by 100887		Inspected by SUNDERMEIER		Standardisation		
Department EL PD								Date 2021-08-30		
								State Final Release		
HARTING D-32339 Espelkamp		Title Han D contacts male/female							Doc-Key / ECM-Nr. 100109246/UGD/004/F 500000201808	
		Type TB		Number 09 15 000 6XXX					Rev. F	
								Page 1/1		