



Part Number : [700581096](#)
Product Description : SL Crimp Terminal, Female,
30-24 AWG, with Tin (Sn) Plated Contact, Bag
Series Number : 70058
Status : Obsolete
Product Category : Crimp Terminals
Packaging Alternative : [700581069](#) (Reel)



Documents and Resources

Specifications

[PS-70058-001.pdf](#)
[PS-70400-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	70058
Description	SL Crimp Terminal, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Bag
Application	Signal
Product Name	CyClone,SL
UPC	191128284349

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.075/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size (AWG)	24, 26, 28, 30
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings	<u>70066</u>

and CPA Retainers	
SL Dual Row Crimp Housings	<u>70450</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for SL Crimp Terminals, 30-24 AWG	<u>2002187000</u>

This document was generated on Apr 13, 2026

Obsolete