


REV.	DATE	ECR NO.	DESCRIPTION
NC	05/30/00	—	INITIAL RELEASE
NC	04/30/08	100012	UPDATE DRAWING FORMAT



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .213"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	GRS	04/30/08											
7	FERRULE	COPPER	GOLD	1		CHECKED													
6	HEX NUT	BRASS	GOLD	1							PART DESCRIPTION								
5	LOCK WASHER	BRASS	GOLD	1							SMA BULKHEAD CRIMP JACK O-RING SEAL (FOR RG-58C/U, 58/U CABLE)								
4	GASKET	SILICONE	RED	1															
3	CONTACT PIN	BER. COPPER	GOLD	1							PART NO.								
2	INSULATOR	PTFE	NATURAL	1							132280								
1	BODY	BRASS	GOLD	1						DWG. NO.		132280.DWG		REV.	A	SIZE	A	SCALE	NA
DESCRIPTION					MATERIAL	FINISH	QTY	C:/132/132280.DWG											