

HDBaseT HDMI over Cat5e/6/6a Extender Receiver, Serial and IR, 4K x 2K UHD/1080p, Up to 500 ft. (150 m), TAA

MODEL NUMBER: BHDBT-R-SI-ER



Works with a Tripp Lite HDBaseT matrix transmitter to extend uncompressed HDMI video and audio, RS-232 serial and IR remote control signals over a Cat5e/6/6a cable up to 500 ft. to a projector, monitor or television.

Description

The BHDBT-R-SI-ER HDBaseT Extender Receiver works in tandem with the Tripp Lite BHDBT-Series matrix transmitter in your HDBaseT installation to extend uncompressed HDMI video and audio, RS-232 serial and IR remote control signals.

Using a single Cat5e/6/6a cable, the BHDBT-R-SI-ER can extend a 1920 x 1080 (1080p) signal up to 500 feet (150 m). To further extend and expand your installation, you can insert up to five BHDBT-TR-SI-ER Extender Transceivers between the receiver and transmitter for a total range up to 3,000 feet (1080p) with a monitor connected to each transceiver.

You can control RS-232 serial devices, such as touchscreen displays or scanners, at baud rates up to 115 Kbps. The 2-way IR Remote Control feature (@ 39 KHz) lets you also control your Blu-ray player using its remote when at the remote monitor and vice versa. The monitor connects to the rear locking HDMI port (ideal for use with Tripp Lite's P569-006-LOCK High-Speed HDMI cables with locking connectors) that prevents the cable from coming loose or undone, ensuring an intact signal.

The BHDBT-R-SI-ER supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP. Included mounting hardware lets you attach the receiver to a wall, rack or pole. Sets up quickly with no software to download or install.

Features

Supports the Latest Video and Audio Applications

- Connects to Tripp Lite BHDBT-Series matrix transmitter with a single Cat5e/6/6a cable

Highlights

- Extends a 1080p @ 60 Hz signal up to 500 ft. (150 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Locking HDMI port ensures an intact signal
- Mounts easily to wall, rack or pole
- Plug and play—no software or drivers to install

Package Includes

- BHDBT-R-SI-ER HDBaseT HDMI over Cat5e/6/6a Extender Receiver
- IR-IN cable
- IR-OUT cable
- 3.5 mm Male to DB9 Female adapter cable
- 3.5 mm Male to DB9 Male adapter cable
- External Power Supply with NEMA 1-15P Plug (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 3A)
- Mounting hardware
- Owner's Manual



Powering Business Worldwide



- Extends a High Definition 1920 x 1080 (1080p) @ 60 Hz signal up to 500 ft. (150 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports 36-bit Deep Color (12 bits per channel), CEC pass-through, 3D video, EDID and HDCP
- Add up to 5 BHDBT-TR-SI-ER Extender Transceivers to further expand the range of your installation up to 3,000 ft. (1080p) with a monitor attached to each transceiver

Allows You to Control Other Devices

- 2-way 39 KHz IR Remote Control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)
- RS-232 serial port supports 115 Kbps full-duplex baud rates for devices such as scanners and touchscreen monitors

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Included mounting hardware lets you install each unit on a wall, rack or pole
- Locking HDMI port (ideal for use with Tripp Lite's P569-006-LOCK HDMI cables) prevents cable from coming loose or disconnected, ensuring an intact signal

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332187031
Product Type	Transmitter
Technology	HDBaseT; HDMI; IR
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Max 720P Range (ft)	500
Max 1080P Range (ft)	500
Maximum Signal Range (ft)	500
Maximum Signal Range (m)	152
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	HDMI (FEMALE)



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Black
Included Mounting Accessories	Y
Shipping Dimensions (hwd / in.)	2.20 x 8.40 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 21.34 x 16.51
Shipping Weight (lbs.)	1.34
Shipping Weight (kg)	0.61
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Weight Details	0.55lbs
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	500
Max 480P Range (ft)	500
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500
Max 480i Range (ft)	500
Max 640 x 480 Range (ft)	500
Max 800 x 600 Range (ft)	500
Max 1600 x 1200 Range (ft)	500
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.