

Honeywell Sensing and Control

Search

**2CPSA2A2B**
Cable Pull
(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (21)

Technology

- Electromechanical (9301)
- Flexible Heaters (140)
- Microstructure (1486)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...



Actual product appearance
may vary.

2CPS Series, Cable Pull Safety Switch, Cable, Maintained Left Side, No Actuation Right Side, 2NC/2NO Direct Opening (Switch 1, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO), 1/2 NPT, Gold-plated Contacts, 120 Vac Multi-cluster LED

[Sales & Service](#)[Distributor Inventory](#)[contacts](#)

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

Meet Dr. Larry

[my links](#)

[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

[News Center](#)

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH
Anniversary site

[new products](#)[New Wireless Products](#)

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site](#)
[WGLA and WPMM](#)
[XYR6000™](#)

[find out more](#)

[white papers](#)

[Wireless Switches Offer Unlimited Benefit](#)
[Basic Switches Are Not Created Equal](#)
[Applying Precision Switches Sensors for Medical Devices](#)
[New Ways to Measure Torque](#)
[Choosing Safety Switches](#)
[Specifying Hour Meters](#)

[Need help?](#)

[Click here to contact us](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Product Type	Cable Pull Safety Switch
Actuator	Cable, Maintained Left Side, No Actuation Right Side
Switch Type	2NC/2NO Direct Opening (Switch 1, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO)
Contact Material	Gold-plated
Termination Type	1/2 NPT
Ampere Rating	10 uA to 50 mA Low Energy
Voltage	250 Vac and 60 Vdc max.
Housing Material	Zinc Die-Cast
Series Name	2CPS
Shock	15 G
Vibration	10 Hz to 500 Hz, 5 G
Sealing	IP67; NEMA 1, 4, 12, 13
CSA File #	LR57328
UL File #	E37138, E157416
Agency Approvals and Standards	UL, CE, CSA, SIL 3 capable
Expected Mechanical Life	1 Million
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and Controls and Relays
Contact Block	Removable with Heavy Duty Wiring Receptacles
Indicator	120 Vac Red Multi-cluster LED
Comment	Low Voltage Directive 73/23/EEC, as amended by directive 93/68/EEC. Machinery Directive 98/37/EEC only as the directives relate to the components being used in a safety function. EN60947-1, EN-60947-5-1, EN60947-5-5