

Memory - IBS MC FLASH 2MB - 2729389

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory, 2 Mbyte

Your advantages

- ✓ Program and configuration memory, plug-in

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 170127
GTIN	4017918170127
Weight per Piece (excluding packing)	59.780 g
Custom tariff number	85235110
Country of origin	Taiwan

Technical data

Dimensions

Height	85.6 mm
Depth	3.3 mm
Width	54 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Weight	49.95 g
--------	---------

Memory - IBS MC FLASH 2MB - 2729389

Technical data

General

Supply voltage	5 V DC
Supply voltage range	4.5 V DC ... 5.5 V DC
Memory type	FLASH-EPROM 2 Mbyte
Memory size	2 Mbyte

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27242212
eCl@ss 11.0	27242212
eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	24210100
eCl@ss 5.1	24210100
eCl@ss 6.0	19150700
eCl@ss 7.0	19150702
eCl@ss 9.0	27242212

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606



Memory - IBS MC FLASH 2MB - 2729389

Classifications

UNSPSC

UNSPSC 21.0	32101606
-------------	----------

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>