



**Part Number :** [936010125](#)

**Product Description :** Heavy-Duty Screw Terminal Insert, Male, 3-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21», Grey

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Part Number :** 7203.6101.0


---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:58afb9da-4e01-4cd8-a3b4-957811a0e248
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Screw Terminal Insert, Male, 3-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21», Grey
Component Type	Inserts - Screw Terminal
Insert Series	S-A3/4
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191871936

### Agency

CSA	256883
UL	E249674

### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	230V / 400V
Wire Protection	No

### Physical

Component Size	3A «21x21»
Durability (mating cycles max)	500
Gender	Male

Insert Color	Grey
Material - Contact	Copper Alloy
Material - Gasket	NBR
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	12.200/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	3
Stripping Length	6.00mm
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	0.25 Nm
Wire Size (AWG)	14-20
Wire Size mm <sup>2</sup>	0.50-2.50

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Heavy-Duty Screw Terminal Insert, Female, 3-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21», Grey	<u>936010121</u>

### Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» Hoods and Housings

---

This document was generated on Apr 25, 2026