


REV.	DATE	ECR NO.	DESCRIPTION
NC	07/18/00	XXXXXX	INITIAL RELEASE
A	06/16/03	XXXXXX	ADD CENTER CONTACT HEIGHT/UPDATE DRAWING FORMAT
B	10/17/11	2240	CHANGE CENTER CONTACT O.D. TO Ø0.83MM



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex PART DESCRIPTION MCX R/A P.C. BOARD RECEPT. JACK (3.94MM LEGS – GOLD) – 75 OHM PART NO. 252129–75						
					DRAWN		M.ZHANG							10/17/11	
					CHECKED										
					ISSUED						DWG. NO. 252129–75.DWG REV. B SIZE A SCALE NA				
					SHEET		1 OF 1								
					CAD FILE		C:/CONNEX/252129–75.DWG								

3	CONTACT PIN	BER. COPPER	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY/HOUSING	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY