


DIMENSIONS




TIN LEAD PART NUMBER

PART NUMBER
86093947113H40265E1

LEAD FREE PART NUMBER


PART NUMBER
86093947113H40APLF

TERMINATION



P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



SPECIFICATION 265 = no contact in position : C7-C23
or SPECIFICATION AP=

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

rev	ecn no	dr	date
A	-	-	2001/01/31
B	LS05-001	JTA	2005/03/03
C	LS06-0095	LGO	2006/06/26
D	ELX-I-41744	MJA	2021/07/21
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	European Views	
		TOLERANCES UNLESS OTHERWISE SPECIFIED		A3	Scale 1.5	
Dr	ROUILLARD	2001/01/31	ANGULAR		ECN	
Eng	TARON	2001/01/31	LINEAR		ELX-I-41744	
Chr	M JACOB	2021/07/21	0.XX' ±2	size	Spec ref -	
Appr	SANOJ	2021/07/21	Product family	DIN 8609		
Amphenol FCI		title STANDARD MALE 3 ROW 94 CONTACTS		dwg no	C-8609-0882	
		catalog no		CUSTOMER		Rev. D
				sheet 1 of 1		