

CATALOG LISTING BE-2R2425 PAGE 1 OF 1 M ISSUE 1		REPLACES X113145-BE RELEASE NO. 201224	MICRO SWITCH a Honeywell Division FED.MFG.CODE 91929	SWITCH – BASIC	CATALOG LISTING BE-2R2425																																																																						
		NOTE 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.139 MAX ON 1.000±.002 CENTERS 2 - CONTACT MATERIAL - SILVER CLAD SILVER CADMIUM OXIDE 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F																																																																									
REVISIONS <table border="1" style="width: 100%; border-collapse: collapse;"> <tr><td style="width: 5%;"> </td><td style="width: 15%;"> </td><td style="width: 15%;"> </td><td style="width: 15%;"> </td><td style="width: 15%;"> </td><td style="width: 15%;"> </td><td style="width: 15%;"> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td><td> </td></tr> </table>																																																																								3X 4-40 UNS THREAD (MOD. PITCH Ø.0930-.0991) ∇.157 MIN IN INSERTS FOR TERMINAL CONNECTIONS			
ANSI Y14.5M-1982 APPLIES																																																																											
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.																																																																											
CHARACTERISTICS OPERATING FORCE — — — 25 OZ MAX DIFFERENTIAL FORCE — — — 1-5 OZ RELEASE FORCE — — — 10 OZ MIN DIFFERENTIAL TRAVEL — — .0002-.0016 OVERTRAVEL — — — — — .010 MIN		ELECTRICAL DATA CONTACT ARRANGEMENT S P D T 25A 125, 250 480 VAC 1 HP 125 VAC, 2 HP 250 OR 480 VAC PILOT DUTY 750 VA 480 VAC, MAX 60/75°C (Cu)		SCALE FULL DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT .050 LB																																																																							