


Item**Ⓐ** Terminal body:Thermoplastic (UL94V-0)
Item**Ⓑ** Terminal Cover:Thermoplastic (UL94V-0)
Item**Ⓒ** Female contact:PhBz(CuSn), Tin plated

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: us

- ➔ G RoHS compliant (lead<4%)
In copper Alloy
- ➔ 0000: “@” Logo (Standard)
000A: “ANYTEK” Mark
Any special item by customer request.
please contact sales department.

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

POLE	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
B	7.62	15.24	22.86	30.48	38.1	45.72	53.34	60.96	68.58	76.2	83.82	91.44	99.06	106.68	114.3
A	13.34	20.96	28.58	36.2	43.82	51.44	59.06	66.68	74.3	81.92	89.54	97.16	104.78	112.4	120.02
Tol.	±0.15					±0.20					±0.30				