



Part Number : 1301350248

Product Description : Super-Safeway Angled GFCI Outlet Box, F3 (3/4") Cord Grip Body, Including NEMA 5-15 GFCI & Duplex Receptacles with Flip Lids and 15.24m (50.0') Cord Length, 12/3 SOOW Cord

Series Number : 130135

Status : Active

Product Category : Power Distribution

Engineering Number : 3320B123



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution

Series	130135
Description	Super-Safeway Angled GFCI Outlet Box, F3 (3/4") Cord Grip Body, Including NEMA 5-15 GFCI & Duplex Receptacles with Flip Lids and 15.24m (50.0') Cord Length, 12/3 SOOW Cord
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Family	Outlet Boxes
Product Name	Super-Safeway
Type	Angled GFCI Outlet Box
UPC	78678828708

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	120V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	15.24m (50.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	GFCI Duplex