



Pushing Performance
Since 1945

Power Supply Q4/2 F 4G2.5 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 201 0192 01
Specification	Power Supply Q4/2 F 4G2.5 1.5m
HARTING eCatalogue	https://b2b.harting.com/6188201019201

Identification

Element	Energy supply
Specification	Pre-assembled on one side
Connector 1	Han-Compact® Hood
	Side entry
	Han® Q 4/2 Female
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Core structure	4x 2.5 mm²
PE contact	Yes
Field of application	Power cables

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	ae0bdeb2-a56c-4d51-aeb1-e094fa9de4c4
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	2
Net weight	391.5 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140274198
ETIM	EC002587
eCl@ss	27060327 Assembled power cable