



**Part Number :** [1600914120](#)

**Product Description :** MXP120 Backshell, Exit Direction Right, Flange Size NW 7.5, with Cable Tie Access, 4 Circuits

**Series Number :** 160091

**Status :** Active

**Product Category :** Connector Accessories



---

## Documents and Resources

### Drawings

[1600914120\\_sd.pdf](#)

[PK-31302-118-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	160091
Description	MXP120 Backshell, Exit Direction Right, Flange Size NW 7.5, with Cable Tie Access, 4 Circuits
Application	Automotive
Component Type	Cover
Product Name	MXP120 Sealed
UPC	889056640688

### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.220/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

## Mates With / Use With

### Use with Part(s)

Description	Part Number
-------------	-------------

MXP120 Sealed Receptacle Housings	<u>34900</u>
--------------------------------------	--------------

---

This document was generated on May 04, 2026