

PRODUKTE

ALARMS FOR
COMMERCIAL VEHICLES

EARPHONES

HORNS

LOUDSPEAKERS (3)

MICROPHONES (2)

PIEZO DISCS

SENSORS

SIGNAL GENERATORS (5)

EX. PROTECTED SIRENS /
VISUAL ALARMS (3)SIRENS / VISUAL
ALARMS

VIBRATION MOTORS

Startseite » Sirenen / optische Alarme » **B/SL 280**
B/SL 280

High Output Siren



Specifications

More Pictures

Datasheet

Electrical and Acoustical Parameter

Rated Voltage (VDC)	24
Operating Voltage (VDC)	16 – 28
Rated Current max (mA)*	40
Sound Pressure Level (dBA, @ 0.3m)*	Min. 95
Tone	Music
Remark:	*@Rated Voltage.

DIGISOUND-Electronic GmbH

Postfach 20 69 - 22810 Norderstedt

Oststrasse 54 - 22844 Norderstedt

Tel. 040 / 52 68 69 - 0

Fax: 040 / 52 68 69 - 13

contact[at]digisound.de

www.digisound.de

Imprint/Privacy Policy | general terms and conditions

