

Catalog No. 54854BEUB0412

Description: CU TP 2HL LUG 90D LNG No4 1/4B GRY

UPC No 786210319476

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper Two-Hole Lug, 90 Degree Bend Long Barrel, Blind End, Max 35kV, Wire Size #4 AWG, 1/4 Inch Bolt Size, 3/4 Inch Hole Spacing, Tin Plated, Die Code 29, Die Color Code Gray



Representative Image

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	4 AWG
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Gray

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

Dimensions

Stud Size	1/4 in
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	N

by ABB

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	2
AWG size	4

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A