

- Home
- Surface Mount Products ▶
- X2Y Products ▶
- Leaded Capacitors ▶
- High Temp Capacitors ▶
- Technical Notes ▶
- Prototyping Kits ▶
- View Product Catalog
- Product Training
- Environmental Compliance ▶
- Distributor Inventory

X2Y® EMI Filter Capacitor Kit - 0603 Size

Johanson Dielectrics, Inc. has partnered with premiere on-line order provider Digi-key to offer a variety of multi-layer chip capacitor sample kits for proto-type design work. Each kit is grouped by type, size, or voltage and contains a selection of popular values and tolerances. The chips are individually packaged in labeled plastic compartments for easy access. The general range of kit contents is described below. Specific part number details may be found at [Digikey.com](#) or [JohansonDielectrics.com](#)



X2Y® EMI FILTER CAPACITOR KIT - 0603 SIZE				P/N: S-X14CBK	Request this Kit
700 piece sample assortment of selected values from 1.0pF to 0.01µF					
Chip Size	Voltage Rating	Dielectric	Capacitanc Range	Qty / Value	Total Qty
0603	50 - 100 VDC	NPO, X7R	1.0pF to 0.01µF	50 pcs	700 pcs

Johanson may from time-time adjust actual kit contents based on design demand trends.

[<< Return to Prototyping Kits Overview](#)

Part Number Search

part number...

Go

Parameter Search

Volt

Size

Cap Value

Go

Reset



About	Technical Notes	Products	Support	
- Contact Info - Company Info - Sales Rep - Distributors - Careers - RoHS Compliance	- General - Application Notes - Processing - Environmental - X2Y Applications - Product training	- Surface Mount - X2Y technology - Prototyping Kits - Leaded Capacitors - High Temp Capacitors - Full Product Catalog	- Quote Request - Sample Request - Prototyping Kit Request - Hard literature Request - Ask a Technical Question - Purchasing Terms and Conditions	Johanson Dielectrics johansondielectrics.com 15191 Bledsoe St. Sylmar, CA 91342 818-364-9800 phone 818-364-6100 fax