

HPP V4 Hybrid plug 4+3p



Part number	09 45 145 1300
Specification	HPP V4 Hybrid plug 4+3p
HARTING eCatalogue	https://b2b.harting.com/09451451300

Identification

Category	Connector
Series	HARTING PushPull
Identification	Hybrid
Element	Connector
Specification	Straight

Version

Termination method	Crimp termination
Locking type	PushPull
Number of contacts	4
Additional contacts	+ 3 power contacts
Pack contents	With cable gland and crimp contacts

Technical characteristics

Conductor cross-section	AWG 26 Ethernet contacts AWG 20 Power contacts
Rated current	5 A
Rated voltage	48 V
Degree of protection acc. to IEC 60529	IP65 IP67
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s



Pushing Performance

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	23.6 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440307 I/O connector