


插頭部件 (Plug Component)			頭部剥皮尺寸 (Dimensions)			線材規格 (Wire Styles)	尾部剥皮尺寸 (Dimensions)			端子規格 (Terminal Style)	
顏色(Color)	零件描述(Component)	Qty.	內剥(Stripped)	外剥(ROJ)	顏色(Color)	SJT 14AWGx3C 105°C 黑色 (Black) Length : 500±20 (19.7"±0.79")	外剥(ROJ)	內剥(Stripped)	顏色(Color)	規格描述(Instruction)	端子編號(Style No.)
35P 黑色 (Black)	FM-302L (IEC 60320, C13)	1	6 ⁺¹ ₋₀	18 ± 2	黑/Black(L)		50.8±5	6.35±3	黑/Black(L)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	
銅本色 (Brass-Natural)	2.0*4.0 方管端子(GEM 98752A-0) (2.0*4.0 Receptacle Terminal)	3	6 ⁺¹ ₋₀	18 ± 2	白/White(N)		50.8±5	6.35±3	白/White(N)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	
米白色 (Off-White)	GA005-5 品字母插兩件式內模 (Computer 2x4 Serial Housing)	1	6 ⁺¹ ₋₀	18 ± 2	綠/Green(E)		50.8±5	6.35±3	綠/Green(E)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	



			線材印字 (Wire Printed)		充實, 油墨印字 (Un-Fillers, Printing Ink)			CnC Tech, LLC Industrial Cable and Connector Technology			
REV	DATE	REVISE CONTENT	NOTE: 1. Hi-Pot Test : 1500V/1Sec ; <0.5mA. 2. Insulation Resistance Test : DC 500/min>100 meg-ohm. 3. Continuity & Polarization Test : No short circuit, break circuit, displacement. 4. Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening. 5. Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening. 6. All material according to Non-toxic standard.(Material must be RoHS compliant.) 7. "FMC" logo maybe present on C13.	包裝方式 (Packing)		DRAWN <i>Chu8.</i>		CUSTOMER	CnC		
				Tied Hank	See Hank Detail						
				Carton Size	480 x 320 x 180	DATE 08/29-2012	P/N No.		800-1403-2-SJT0-BL-00050		
				Pack Number	200pcs/ UL Laster Labels						
				Carton Print	See Purchase Order						
TYPE		IEC 60320, C13 RA to ROJ(S&R) Power Supply Cord		MATERIAL	PVC	UNIT		mm			
DRAWNING NO.		098MM992					REV		A	Customer Approval	