

K11A39U2, AL Universal Terminal, 2-Conductor, 2-Hole

By Burndy
Catalog # [K11A39U2](#)

Aluminum Universal Terminal, 2 Hole, 2-Conductor: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Spacing, 2 Screws



Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	<ul style="list-style-type: none"> • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil
-------------------------	---

Conductor - AL Str Size Range	750 kcmil
Conductor - Copper Str Size	<ul style="list-style-type: none"> • 1/0 AWG (Str)-750 kcmil • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor Size	1/0 AWG-750 KCMIL
Conductor - Copper Solid Size	<ul style="list-style-type: none"> • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	2
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	1/0 AWG (Str)-750 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Stacked

Dimensions

Dimension - Pad Width inch	1.52 in
Package Height	0.000 in
Dimension - Height mm	76.7 mm
Dimension - Height inch	3.02 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	125 mm


Dimension - Width fraction	1-69/100 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Screw Size inch	13/16
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - Width mm	43 mm
Dimension - Width inch	1.52 in
Dimension - D inch	2.31 in
Dimension - N inch	0.38 in
Dimension - Length Overall inch	4.91 in

Force Related

Installation Torque Recommended in-lb	375 LBS/in
---------------------------------------	------------

General

Material - Hardware	Aluminum
---------------------	----------



Physical Attribute - Screw Type	Allen
Plated	Y
Sub Brand	UNIVERSAL TERM
UPC	781810370292
Type	Bolted Lugs & Terminals
Hex Key	3/8
Material	Aluminum
Plating Type	Tin plated
UPC 12 Digit	781810370292
UPC 14 Digit GTIN	00781810370292

Logistics

Minimum Pack Quantity	1
Pallet Quantity	576
Carton Quantity	18

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

© 2026 Hubbell Incorporated. All rights reserved
BRDY-K11A39U2-SPEC-EN | REV 5/2026