





APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/16/05	
A		REDRAWN	01/23/13	
B		REVISED DIM.	03/27/13	
C		REVISED SHAPE	9/6/13	AY



PANEL THICKNESS	DIMENSIONS	
	A	
.031-.047 [0.80-1.20]	.799	[20.30]
.051-.079 [1.30-2.00]	.807	[20.50]

RECOMMENDED PANEL CUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate overall

Electrical:

Current rating: C-ULus: 15A @ 250V

ENEC & CCC & KC: 10A @250V

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 3,000 VAC for 1 minute

Environmental:

Operating Temp: -40°C to +70°C max.

Lead free, RoHS compliant



TERMINAL OPTIONS			
-1	-2	-3	-5
.187 Q.C.	.250 Q.C.	.157 Solder	.098 Solder

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	6/16/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
IEC MALE INLET, SNAP-IN PANEL MOUNT

SIZE	PART NO.	REV.
X	IEC-C-X	C
REF:	S00087C	SCALE: NTS
SHEET 1 OF 1		