
Part Number : 5601230700
Product Description : DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 7 Circuits
Series Number : 560123
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

5601230700_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-560123-001-001.pdf

PK-560123-001-001.pdf

PS-560123-001-001.pdf (Tin Plating)

PS-560123-003-001.pdf (Tin Plating)

PS-560123-004-000.pdf

5601240131-000.pdf (Gold Plating)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	560123
Description	DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 7 Circuits
Application	Automotive, Wire-to-Board
Component Type	Receptacle
Product Name	DuraClik
UPC	191130507115

Agency

UL	E29179

Physical

Circuits (maximum)	7
Color - Resin	White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	0.414/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +130°C
Terminal Size	0.635

Mates With / Use With

Mates with Part(s)

Description	Part Number
DuraClik Right-Angle Single Row Headers	502352
DuraClik Vertical Single Row Headers	560020

Use with Part(s)

Description	Part Number
DuraClik Wire-to-Board Independent Secondary Lock (ISL) Retainer, 7 Circuits, Gray	5601250700
DuraClik ISL Female Crimp Terminals	560124

Downloaded from Arrow.com.