

D10H4



Article Number: 211-70200

Screw Mount Cable Clip .67" X .31", Max Bun Dia .40", Mnt Hole .31" - POM, Black, 500/pk

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	D10H4
Type	8D10
Color	Black (BK)
Features and Benefits	Available in three sizes, HellermannTyton screw mount clips offer quick, snap-in action. These clips allow for easy release for wiring changes or replacements, saving both time and money.
Short Description	Screw Mount Cable Clip .67" X .31", Max Bun Dia .40", Mnt Hole .31" - POM, Black, 500/pk

Product Dimensions

Length L (Imperial)	0.67 "
Length L (Metric)	17.0 mm
Length L2 (Imperial)	0.31 "
Length L2 (Metric)	8.0 mm
Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.6 "
Width W (Metric)	15.0 mm

Bundle Diameter Max. (Imperial)	0.4 "
Bundle Diameter Max. (Metric)	10.0 mm

Mounting Hole Diameter D (Imperial)	0.31 "
Mounting Hole Diameter D (Metric)	8.0 mm
Nominal Diameter (Imperial)	3/8 "
Nominal Diameter (Metric)	10 mm
Wall Thickness WT (Imperial)	.08 "
Wall Thickness WT (Metric)	2.0 mm
Mounting Hole Diameter D Max. (Metric)	8.0 mm
Mounting Hole Diameter D Min. (Metric)	8.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	500 Pieces
Carton Quantity	6000 Pieces
Weight (Metric)	2.5 kg

Material and Specifications

Material	Polyacetal (POM)
Material Shortcut	POM
Flammability	UL94 HB
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
ROHS Compliant	Yes