

Search within category

GO

BUY NOW

DESIGN / INSTALL



ISTPH6X1.5MBL

Patch Cord, IndustrialNET, Cat6A, Shielded, 600V, RJ45 plug to RJ45 plug, Black, 1.5meter

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Conductor Gauge (AWG)	NA
Conductor Gauge (kcmil)	26
Performance Level	Category 6A
Conductor Type	Stranded
Cable Construction	NA
Patch Cord Type	Shielded
Plug Housing Material	Polycarbonate
Jacket Material	Thermoplastic Elastomer
Connector 2 Type	Modular Plug
Connector 1 Type	Modular Plug
Overall Length (In.)	59.4
Overall Length (ft.)	4.95
Overall Length (m)	1.5
Overall Length (mm)	NA
Nominal Diameter (In.)	0.29
Nominal Diameter (mm)	7.4
Wiring Scheme	T568B
Maximum Operating Temperature (°C)	60
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Boot Color	NA
Color	Black
Sub Brand	IndustrialNet

Flammability Rating	CM
Standards Met	ANSI/TIA-568-C.2 Category 6A and ISO 11801 Class Ea standards at swept frequencies up to 500MHz;ANSI/TIA-968-A requirements; IEC 60603-7 UL-rated: UL 1863; IEEE 802.3af and IEEE 802.3at for PoE applications
IP Rating	IP 20
NEMA Rating	NA
IEC Variant	IEC 60603-7
PoE Compatibility	PoE+
Product Type	Industrial Copper Patch Cord
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
Measurement System	Meters (Rest of World)