

Part Number : 1301110027

Product Description : Safety Yellow Molded Stringlight, 200W, 14/2 SJTW with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0')

Series Number : 130111

Status : Obsolete

Product Category : Lamps and Lights

Engineering Number : 5000



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

---

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

---

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

---

#### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Obsolete
Category	Lamps and Lights
Series	130111
Description	Safety Yellow Molded Stringlight, 200W, 14/2 SJTW with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0')
NEMA Configuration	NEMA 1-15
NEMA Rating	Rain Tight
Product Family	Stringlights
Product Name	Safety Yellow
Type	String Lights
UPC	78678840867

## Agency

UL	E112216
----	---------

## Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Incandescent
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Cord Type - Primary	14/2 SJTW
Depth	N/A
Duty	Commercial
Guard Included	Yes
Guard Type	Polypropylene
Height	N/A
Lamp Type	A21

Length	30.48m (100.0')
Material - Guard	Polypropylene
Mounting Style	Stringer
Net Weight	1254.000/g
Outlet	None
Packaging Type	Carton
Socket Construction	Molded

---

---

This document was generated on Dec 16, 2023