








FCIconnect.com

Copyright FCI



GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000


LEAD FREE PART NUMBER

Part number	D50S24A*PX00LF
-------------	----------------

Plating: 4 --> Flash Au
Plating: 6 --> 0.76µ Au

Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

mat'l. code —				surface — ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB										
ltr	ecn no	dr	date	tolerances unless		otherwise specified			title FEMALE CONNECTOR DELTA D—50 STRAIGHT SOLDER											
D	ELX-I-22878	AB	2015/01/06	angles	linear	.0±0.1														
—	—	—	—			.00±0.1														
—	—	—	—			.000±0.1														
				0°±2°				scale 2:1												
— — — —				dr	BOULTIER		1997/11/04		dwg no						sheet 1 of 1		size 5			
— — — —				enr	MITHUN PAUL		2015/01/06		C01—8646—0600						A3					
— — — —				chr	MITHUN PAUL		2015/01/06													
— — — —				appd	BIJU K PAUL		2015/01/06													
sheet index		revision	D																	
		sheet	1																	