



Part Number : [1301110024](#)
Product Description : Pro-Yellow Stringlight, 150W, 12/2 TC2 with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0'), cULus Listed
Series Number : 130111
Status : Active
Product Category : Lamps and Lights
Engineering Number : 302SRL



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130111
Description	Pro-Yellow Stringlight, 150W, 12/2 TC2 with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0'), cULus Listed
NEMA Configuration	NEMA 1-15
NEMA Rating	Rain Tight
Product Name	Pro-Yellow
Type	String Lights
UPC	78678861202

Agency

UL	E112216
----	---------

Electrical

Lamp Wattage - Maximum	150W
Lumens	1500
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Cord Type - Primary	12/2 TC
Depth	N/A
Duty	General
Guard Included	Yes

Guard Type	Polypropylene
Height	N/A
Lamp Type	A21
Length	30.48m (100.0')
Material - Guard	Polypropylene
Mounting Style	Stringer
Net Weight	1.360/kg
Outlet	None
Packaging Type	Carton
Socket Construction	Assembled

This document was generated on Sep 17, 2025