

## RAFIX 22 FS<sup>+</sup>, potentiometer-type drive, round collar



### fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Vehicle construction
- Handheld terminals
- Industrial robots

### special features

- For potentiometer with shaft diameter 6 mm and 50 mm axis length.
- Potentiometer not supplied.



### description

For potentiometers with a 6 mm shaft diameter and 50 mm axle length. Potentiometer not supplied.

### technical data

#### ➤ general

Collar shape	round
Operating temperature, min.	-25 °C
Storage temperature, min.	-40 °C
Operating temperature, max.	70 °C
Storage temperature, max.	80 °C
illuminated	No
Packaging	Box
Packaging unit	5 pcs.
net weight	17.4 g
Degree of protection, front side, according to DIN EN 60529	IP65
UL Enclosure Type Rating front side	type 1 type 4X
Environment resistance	IEC 60068-2-14 IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78
Salt-spray resistance according to standard	IEC 60068-2-11
MOQ order	20 pcs.
RoHS compliant	Yes
REACH compliant	Yes

#### ➤ mounting diameters

Mounting hole	22.3 mm
Installation height	26 mm
Grid, min.	30 x 30 mm

### direct links

- [RAFI eCatalog](#)


Outside dimension, length	29.8 mm
Outside dimension, width	29.8 mm
Collar dimension	ø 29,8 mm

**> mechanical data**


Fixing	Threaded ring
Threaded ring torque, max.	1.2 Nm

## drawings

### Dimensioned drawing



### System drawing



## System drawing



## Mounting hole drawing



acc. to IEC 60947-5-1

## front panel drawing

