Data sheet

MULTI-STRIPAX 0.25-1.5S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9204540000
Type	MULTI-STRIPAX 0.25-1.5S
GTIN (EAN)	4032248671083
Qty.	1 items

Downloaded from Arrow.com.

MULTI-STRIPAX 0.25-1.5S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	250 mm	Width (inches)	9.8425 inch
Net weight	556 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping and cutting tool for VDE cables with PVC insulation, 0.25 - 1.5 mm²

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm²
max. cutting capacity, solid	2.5 mm²	max. cutting capacity, fine-strand	6 mm²
max. cutting capacity, ribbon	10,2 mm x 4 mm	Stripping range AWG, max.	14 AWG
Stripping range AWG, min.	23 AWG	Stripping length, min.	2 mm
Conductor cross-section, max.	1.5 mm²	Conductor cross-section, min.	25 mm²

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

Downloaded from Arrow.com.


MULTI-STRIPAX 0.25-1.5S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Downloaded from Arrow.com.